




ASSEMBLY INSTRUCTIONS


UltraHD® Interlocking Height Adjustable Workbench

(Model No. 20120)

48 in W x 20 in D x 30-39 in H













(1.22 m W x 50.8 cm D x 76.2-99 cm H)





PARTS LIST

Please check the parts carefully according to the parts list. If you are missing any parts, please call our customer service department (please refer to page 8).

	
(#1) Bottom Crossbar x 1 PC	(#2) Top Crossbar x 2 PCS
	
(#3) Wood Top x 1 PC	(#5) Leg x 2 PCS
	
(#6) Leveling Feet x 4 PCS	(#8) Linkage Plate x 2 PCS
	
(#27-B) Washer x 20 PCS	(#40) Screw (M8 x 18L) x 20 PCS
	
(#9) Hand Twist Screw (M4 x 12L) x 2 PCS	(#61) Screw (M4 x 12L) x 2PCS
	
(#25) Wrench x 1 PC	(#21)Screwdriver x 1PC

UltraHD® Interlocking Height Adjustable Workbench | Table (Model No. 20120)




***NOTE:** We recommend TWO people for assembly.

Step 1. Assemble Top Crossbar (#2)

Open the package and make sure there are no missing parts. We recommend assembling in an area with enough space to complete the unit.

Place the Wood Top (#3) on top of the cardboard to protect it from scratches during assembly.


Attach both Top Crossbars (#2) to the Wood Top (#3). Use 8 pcs of Screw M8 x 18L (#40) with Washers (#27-B). Use Wrench (#25) to tighten.



Step 2. Adjust the Height of the Legs (#5)



1. Remove the pre-installed Hand Knobs and Washers (#27-B) on each Leg (#5), adjust the Legs (#5) to your desired height. The Legs can be adjusted from 30 in. to 39 in.

2. Insert all 4 Hand Knobs and Washers (#27-B) back into the leg tubes.



Step 3. Assemble Legs (#5)

Attach both Legs (#5) into the tube on the Top Crossbars (#2) as the left photo shows. Line up the screw holes, use 8 pcs of Screw M8 x 18L (#40) and Washers (#27-B). Use Wrench (#25) to tighten.




UltraHD® Interlocking Height Adjustable Workbench | Table (Model No. 20120)



***NOTE:** We recommend TWO people for assembly.


Step 4. Assemble Bottom Crossbar (#1)

Place the Bottom Crossbar (#1) to the back of the Legs (#5). Line up the screw holes, use 4 pcs of Screw M8 x 18L (#40) with Washers (#27-B) to attach. Use Wrench (#25) to tighten.




Step 5. Attach Leveling Feet (#6)

Insert the Leveling Feet (#6) into the Legs (#5). Use Wrench (#25) to tighten.



Linkage Plates (#8) can be used to interlock two or more workbenches together. If you are **NOT** planning on interlocking workbenches, we recommend installing Linkage Plates (#8) for future use, as shown in illustration to the left, using 2 pcs of Hand Twist Screw (#9) and 2 pcs of Screw (M4 x 12L) (#61).




See page 5, for instruction on interlocking two or more workbenches.

UltraHD® Interlocking Height Adjustable Workbench | Table (Model No. 20120)




***NOTE: We recommend TWO people for assembly.**


If you have two or more workbenches/tables, here are some options to connect them together.



Option A





Option B



Option A. Connecting Side-by-Side


1. Remove the Hand Twist Screw (#9) and loosen the Screw M4 x 12L (#61) on the Linkage Plates (#8).




UltraHD® Interlocking Height Adjustable Workbench | Table (Model No. 20120)




***NOTE:** We recommend TWO people for assembly.



2. Rotate the Linkage Plates (#8) outward by 90 degrees.



Note: Before connecting the Workbenches/Tables, use the Wrench (#25) to adjust the Leveling Feet (#6) to ensure the workbench surfaces are flush.




3. Connect two Workbenches/Tables together. Insert Hand Twist Screw (#9) into the connecting Workbench/Table and tighten. Then, tighten Screw M4 x 12L (#61) with Screwdriver (#21). Make sure the front and back edges of the Wood Tops (#3) are flush before tightening.


UltraHD® Interlocking Height Adjustable Workbench | Table (Model No. 20120)



***NOTE: We recommend TWO people for assembly.**




Option B. Connecting Back to Back




1. Remove the Hand Twist Screw (#9) and the Screw M4 x 12L (#61) on the Linkage Plates (#8).

You will install the Linkage Plates (#8) into the back Top Crossbar (#2) as the image/instructions are shown below.



2. Connect two Workbenches/Tables back to back. Make sure the side edges of the Wood Tops (#3) are flush. Then, place the Linkage Plates on both of the Top Crossbars (#2). Insert a Hand Twist Screw (#9) and Screw M4 x 12L (#61) into the connecting Workbench/Table to secure.



CONTACT INFORMATION


If you are missing any parts, have any questions, or need additional assistance in assembly, please contact our bilingual (English and Spanish) customer service department at:




Seville Classics, Inc.
19401 Harborage Way Torrance, CA 90501 USA
Telephone: (800) 323-5565 within USA
Fax: (310) 533-3899
Hours: 9:00am - 4:30pm (Pacific Standard Time)
E-mail: support@sevilleclassics.com
Website & Online Store: www.sevilleclassics.com

*****Please visit our website or call and inquire about our additional UltraHD Line*****

UltraHD® Line




UltraHD® Tall Storage Cabinet
Model No. 16236 (Granite)
Model No. 20143 (Graphite)
Model No. 20153 (Red)
Model No. 20133 (White)




UltraHD® Mega Storage Cabinet
Model No. 16238 (Granite)
Model No. 20148 (Graphite)
Model No. 20158 (Red)
Model No. 20138 (White)

UltraHD® Line




UltraHD® Rolling Cabinet

Model No. 20225 (Granite)
Model No. 20081 (Graphite)
Model No. 20082 (Red)
Model No. 20083 (White)




UltraHD® 6-Foot Height Adjustable Workbench

Model No. 20292 (Granite)
Model No. 20293 (Graphite)
Model No. 20134 (Red)
Model No. 20131 (White)




UltraHD® Wall Cabinet with Open Shelf

Model No. 20230 (Granite)
Model No. 20140 (Graphite)
Model No. 20150 (Red)
Model No. 20130 (White)




UltraHD® 2-Door Rolling Workbench

Model No. 20262 (Granite)
Model No. 20142 (Graphite)
Model No. 20152 (Red)
Model No. 20132 (White)



UltraHD® Rolling Trash Bin

Model No. 20215



UltraHD® Lighted Workcenter

Model No. 20247 (Granite)
Model No. 20246 (Graphite)
Model No. 20157 (Red)
Model No. 20291 (White)